

# FLASKS FREEZE DRYING

Complete "fast-freeze" flask with snap-on rubber cap and plain or stopcock PTFE adapter. Flasks are designed for ease of handling and faster loading. Wide mouth provides easy access to inner walls. Snap-on black rubber cap is grease free; one size fits all capacity flasks. Plain straight adapter for connecting flask cap to lyophilizer manifold is removable.

#### 7035 Series Flasks

- Compatible with all major brands of freeze dryers and manifolds
- · Uniform wall weight for good temperature transfer
- · Wide mouth provides ease in getting product in and out of the flask
- Black rubber cap matches O.D. and I.D. on the flask
- PTFE adapter tubes available plain or with stopcock
- · Caps fit standard lyophilizer manifolds

**Contact us for...** Custom glass and repair services.



## TWISTLOR ACE-SEAL FREEZE DRYING

These are just a few of the more widely used glassware components to replace your existing glass. All our rotary evaporator replacement glass is manufactured in the USA, to exacting specifications and standards.

### 7030 Series Flasks

- O-Ring for vacuum-tight seal
- Dual purpose: Rotary evaporator and freeze drying flask
- Adapter heads will fit all capacity flasks
- · Adapter head comes with nylon retainers and FETFE O-Ring
- Note: These flasks are NOT for use in elevated temperatures

#### Also Available...

Contact us for all your freeze drying and rotavap glassware needs, for both large and bench scale applications.



1430 Northwest Boulevard Vineland, NJ 08360 sales@aceglass.com P: (800) 223-4524 F: (800) 543-6752

© 2023 Ace Glass Inc. All rights reserved. 09/22/2023 F1029R