

Deuterium halogen light source



- *Integrated deuterium and halogen light source*
- *Compact and rugged*
- *Spectrometer controlled*
- *Easy lamp replacement*
- *Integrated shutter*

Mini-DH is a deuterium tungsten halogen light source optimized for fiber optic coupling. Light source functions can be controlled by the spectrometer. The deuterium and tungsten lamps can be operated individually or together. This is an ideal light source for transmission measurements. The Mini-DH has an integrated TTL shutter that facilitates the taking of dark background spectra.

Part number

Mini-DH

Control Development, Inc., reserves the right to change specifications without notice.

Control Development, Inc.
2633 Foundation Drive, South Bend, IN 46628
Phone: (574) 288-7338 Fax: (574) 288-7339
www.controldevelopment.com
sales@controldevelopment.com

